

PULSATRON KC3

TECHNICAL DATA

Dimensions (mm)

Overall - length (front to back)	162
Overall - width (left to right)	265
Overall - height	250
Tank (Basket) - length (front to back)	135 (103)
Tank (Basket) - width (left to right)	238 (180)
Tank (Basket) - depth	100 (63)
Selectable temperature	-
Heater power	-
Operating frequency	38 kHz +/- 10%
Sonics timing (mins)	-
Power (RMS)	85W
Drain facility	-
Weight (kg)	3.6
Mains input / frequency	220/240V 50 Hz
Accessories	
Plug and lead set	included in price of bath
Basket, plastic coated stainless steel	Optional
Lid, stainless steel with handle	Optional
Beaker holder	-
Beaker, 600ml Pyrex	-

Baths are supplied with a free starter pack of general purpose cleaning agent (UK only). This is only one of a range of ultrasonic baths and tanks available from Guyson, please call for further information.



GUYSON

PULSATRON KC BATHS

- Safe, fast and effective cleaning
- Inexpensive and efficient
- Robust and reliable
- 2 year warranty

Guyson's Kerry Pulsatron KC ultrasonic baths offer the performance and reliability needed to meet the demands of many applications.

They are particularly suitable for applications within the following fields:

- Medical
- Optical
- Dental
- Industrial

The KC3 ultrasonic bath has an approximate capacity of 3 litres, it is easy to use, with a single on/off switch for the ultrasonics. Operating instructions are printed on the bath's front panel.

In operation cleaning of lightly soiled items such as jewellery may take only seconds. Removal of medium soil may take two or more minutes.

Key Features

- Integral Guyson Pulsatron high efficiency generators with automatic tuning for powerful cleaning action.
- Baths rated for continuous use if required.
- Dual-purpose fail-safe, resettable thermal fuse - protects against over temperature operation / low liquid level.
- CE compliant.



FM 38758

ISO 9001:2008

PULSATRON KC3



Modifications and improvements to Guyson machines are introduced from time to time as a direct result of our policy of continuous development. Consequently all designs and specifications quoted must be regarded as subject to change. Please refer to quotation.

Ref: KC3 10/09

Guyson International Ltd. Tel: 01756 799911

www.guyson.co.uk

